










Werkzeugliste für Aderendhülsen zur richtigen Verdringung nach UL

Zwilling-Aderendhülsen, Einzelbeutel

(BN 22496, BN 22497, BN 22498, BN 22465, BN 22466, BN 22467)

 □ mm ²	L1	AWG	Abisolier- länge [mm]	Leiter- klasse für UL486F								
					Crimpit F 6 L BN 20766 Art-# 9032433	Crimpit F 25 L BN 20766 Art-# 9032434	Crimpit F 50 L BN 20766 Art-# 9032475	Crimpit F 6 EN BN 20767 Art-# 9032447	Crimpit F 16 BN 20767 Art-# 9032448	Crimpit F 50 EN BN 20767 Art-# 9032432	PZ 10 SQR BN 20768 Art-# 9032505	PZ 10 HEX BN 20769 Art-# 9032506
2 x 0,34	8	2 x 22	11	B								
2 x 0,5	8	2 x 21	11	B								
2 x 0,5	10	2 x 21	14	B								
2 x 0,5	12	2 x 21	16	B								
2 x 0,75	8	2 x 19	11	B								
2 x 0,75	10	2 x 19	14	B								
2 x 0,75	12	2 x 19	16	B								
2 x 0,75	18	2 x 19	22	B								
2 x 1	8	2 x 18	11	B								
2 x 1	12	2 x 18	16	B								
2 x 1	14	2 x 18	18	B								
2 x 1	18	2 x 18	22	B								
2 x 1,5	8	2 x 16	11	B, K								
2 x 1,5	12	2 x 16	17	B, K								
2 x 1,5	18	2 x 16	22	B, K								
2 x 2,5	10	2 x 14	14	B, K								
2 x 2,5	12	2 x 14	16	B, K								
2 x 2,5	18	2 x 14	22	B, K								
2 x 4	12	2 x 12	17	C, K								
2 x 4	18	2 x 12	22	C, K								
2 x 6	12	2 x 10	17	C, K								
2 x 6	18	2 x 10	22	C, K								
2 x 10	12	2 x 8	17	K								
2 x 10	18	2 x 8	22	K								
2 x 16	16	2 x 6	22	K								
2 x 16	25	2 x 6	31	K								