

BENZING

Retaining rings and assembly tool

Which retaining ring can be installed with which assembly tool, according to DIN 6799

 Assembly tools for retaining rings type **SS** and **BS** are available on request.

	Article number	Nominal Dimension	Article number	Article number
BN-809 Circlips for shafts bulk 	1284592	0,8	1412272	1412418
	1284606	1,2	1412280	1412426
	1284614	1,5	1412299	1412434
	1284622	1,9	1412302	1412442
	1284630	2,3	1412310	1412450
	1284649	3,2	1412329	1412469
	1284657	4	1412337	1412477
	1284665	5	1412345	1412485
	1284673	6	1412353	1412493
	1284681	7	1412361	1412507
	1284703	8	1412388	1412515
	1284711	9	On request	1412523
	1284738	10	On request	1412531
	1284746	12	On request	9092290
	1284754	15	On request	On request
	1284762	19	On request	On request
	1284770	24	On request	On request
	1284789	30	On request	On request
BN-810 Circlips for shafts bulk 	1284800	1,5	1412299	1412434
	1284819	1,9	1412302	1412442
	1284827	2,3	1412310	1412450
	1284835	3,2	1412329	1412469
	1284843	4	1412337	1412477
	1284851	5	1412345	1412485
	1284878	6	1412353	1412493
	1284886	7	1412361	1412507
	1284894	8	1412388	1412515
	1284908	9	On request	1412523
	1284916	10	On request	1412531
	1284924	12	On request	9092290
	1284932	15	On request	On request
	1284940	19	On request	On request
	1284959	24	On request	On request

BN-1179

Benzing
Applicators for circlips DIN 6799
short

**BN-1180**

Benzing
Applicators for circlips DIN 6799
long



	Article number	Nominal Dimension	Article number	Article number
BN-811 Circlips for shafts stacked 	1284967	0,8	1412272	1412418
	1284975	1,2	1412280	1412426
	1284983	1,5	1412299	1412434
	1284991	1,9	1412302	1412442
	1285009	2,3	1412310	1412450
	1285017	3,2	1412329	1412469
	1285025	4	1412337	1412477
	1285033	5	1412345	1412485
	1285041	6	1412353	1412493
	1285068	7	1412361	1412507
	1285076	8	1412388	1412515
	1285084	9	On request	1412523
	1285092	10	On request	1412531
BN-812 Circlips for shafts stacked 	1285114	1,5	1412299	1412434
	1285122	1,9	1412302	1412442
	1285130	2,3	1412310	1412450
	1285149	3,2	1412329	1412469
	1285157	4	1412337	1412477
	1285165	5	1412345	1412485
	1285173	6	1412353	1412493
	1285181	7	1412361	1412507
	1285203	8	1412388	1412515
	1285211	9	On request	1412523
	1285238	10	On request	1412531
BN-679 Circlips for shafts bulk 	1254464	1,2	1412280	1412426
	1254472	1,5	1412299	1412434
	1254480	1,9	1412302	1412442
	1254499	2,3	1412310	1412450
	1254502	3,2	1412329	1412469
	1254510	4	1412337	1412477
	1254529	5	1412345	1412485
	1254537	6	1412353	1412493
	1254545	7	1412361	1412507
	1254553	8	1412388	1412515
	1254561	9	On request	1412523
	1254588	10	On request	1412531
	1254596	12	On request	9092290
	1254618	15	On request	On request
	1254626	19	On request	On request
	1254634	24	On request	On request

BN-1179

Benzing
Applicators for circlips DIN 6799
short



BN-1180

Benzing
Applicators for circlips DIN 6799
long



			BN-1179 Benzing Applicators for circlips DIN 6799 short	BN-1180 Benzing Applicators for circlips DIN 6799 long
				
	Article number	Nominal Dimension	Article number	Article number
BN-681 Circlips for shafts bulk 	1254650	1,2	1412280	1412426
	1254669	1,5	1412299	1412434
	1254677	1,9	1412302	1412442
	1254685	2,3	1412310	1412450
	1254693	3,2	1412329	1412469
	1254707	4	1412337	1412477
	1254715	5	1412345	1412485
	1254723	6	1412353	1412493
	1254731	7	1412361	1412507
	1254758	8	1412388	1412515
	1254766	9	On request	1412523
	1254774	10	On request	1412531
	1254782	12	On request	9092290
	1254790	15	On request	On request
	1254812	24	On request	On request
BN-680 Circlips for shafts stacked 	1255398	1,2	1412280	1412426
	1255401	1,5	1412299	1412434
	1255428	1,9	1412302	1412442
	1255436	2,3	1412310	1412450
	1255444	3,2	1412329	1412469
	1255452	4	1412337	1412477
	1255460	5	1412345	1412485
	1255479	6	1412353	1412493
	1255487	7	1412361	1412507
	1255495	8	1412388	1412515
	1255509	9	On request	1412523
	9076141	10	On request	1412531
	9052350	12	On request	9092290
BN-1355 Circlips for shafts stacked 	9092375	1,2	1412280	1412426
	1117041	1,9	1412302	1412434
	1117068	2,3	1412310	1412442
	1117076	3,2	1412329	1412450
	1117084	4	1412337	1412469
	1117092	5	1412345	1412477
	1117106	6	1412353	1412485

			BN-1179 Benzing Applicators for circlips DIN 6799 short	BN-1180 Benzing Applicators for circlips DIN 6799 long
				
	Article number	Nominal Dimension	Article number	Article number
BN-592 Circlips for shafts bulk 	1227858	1,2	1412280	1412426
	1227866	1,5	1412299	1412434
	1227874	1,9	1412302	1412442
	1227882	2,3	1412310	1412450
	1227890	3,2	1412329	1412469
	1227904	4	1412337	1412477
	1227912	5	1412345	1412485
	1227920	6	1412353	1412493
	1227939	7	1412361	1412507
	1227947	8	1412388	1412515
	1227955	9	On request	1412523
	1227963	10	On request	1412531
	1227971	12	On request	9092290
	1227998	15	On request	On request
BN-593 Circlips for shafts stacked 	3587038	0,8	1412272	1412418
	1228056	1,2	1412280	1412426
	1228064	1,5	1412299	1412434
	1228072	1,9	1412302	1412442
	1228080	2,3	1412310	1412450
	1228099	3,2	1412329	1412469
	1228102	4	1412337	1412477
	1228110	5	1412345	1412485
	1228129	6	1412353	1412493
	1228137	7	1412361	1412507
	1228145	8	1412388	1412515