










弹簧销连接的静态剪切载荷


公称直径 [mm]	卷制弹性圆柱销		直槽弹簧销	
	标准型, 参照ISO 8750	重型, 参照ISO 8748	重型, 参照ISO 8752	轻型, 参照ISO 13337
			公称直径小于等于8 mm   公称直径大于等于10 mm 	公称直径小于等于8 mm   公称直径大于等于10 mm 
	弹簧钢硬化、回火硬度420至545HV		弹簧钢硬化、回火硬度420至560HV	
0,8	0,2	-	-	-
1	0,3	-	0,35	-
1,2	0,45	-	-	-
1,5	0,72	0,95	0,79	-
2	1,25	1,75	1,41	0,75
2,5	1,95	2,75	2,19	1,2
3	2,25	3,8	3,16	1,75
3,5	3,75	-	4,53	2,3
4	4,8	6,75	5,62	4
4,5	-	-	7,68	4,4
5	7,5	10	8,77	5,2
6	11	15	13	9
8	19,5	26,5	21,38	12
10	31	42	35,08	20
12	44,5	60	52,07	24
13	-	-	57,55	33
14	60	82,5	72,36	42
16	77,5	105	85,51	49
18	-	-	111,27	63
20	125	170	140,32	79

卷制弹性圆柱销




1. 图示径向弹力
2. 插入前的销
3. 插入后的销
4. 销被敲出后恢复原状
5. 内六型扳手的万向节
6. 卷制销

单面连接



双面连接



开槽弹簧销的定位

