



# PERRY JOHNSON LABORATORY ACCREDITATION, INC.

## Certificate of Accreditation

*Perry Johnson Laboratory Accreditation, Inc. has assessed the Laboratory of:*

### ***Bossard***

***6521 Production Drive, Cedar Falls, IA 50613***

*(Hereinafter called the Organization) and hereby declares that Organization is accredited in accordance with the recognized International Standard:*

### **ISO/IEC 17025:2017**

This accreditation demonstrates technical competence for a defined scope and the operation of a laboratory quality management system (as outlined by the joint ISO-ILAC-IAF Communiqué dated April 2017):

***Dimensional Inspections and Mechanical Testing of Threaded Fasteners, Washers, Rivets, and Related Hardware***  
*(As detailed in the supplement)*

Accreditation claims for such testing and/or calibration services shall only be made from addresses referenced within this certificate. This Accreditation is granted subject to the system rules governing the Accreditation referred to above, and the Organization hereby covenants with the Accreditation body's duty to observe and comply with the said rules.

For PJLA:

Tracy Szerszen  
President

*Initial Accreditation Date:*

August 5, 2009

*Issue Date:*

January 5, 2022

*Expiration Date:*

March 31, 2024

*Accreditation No.:*

60247

*Certificate No.:*

L21-809

Perry Johnson Laboratory  
Accreditation, Inc. (PJLA)  
755 W. Big Beaver, Suite 1325  
Troy, Michigan 48084

*The validity of this certificate is maintained through ongoing assessments based on a continuous accreditation cycle. The validity of this certificate should be confirmed through the PJLA website: [www.pjllabs.com](http://www.pjllabs.com)*



# Certificate of Accreditation: Supplement

## Bossard

6521 Production Drive, Cedar, IA 50613  
 Contact Name: Stacey Booth Phone: 319-277-5520

Accreditation is granted to the facility to perform the following testing:

FIELD OF TEST	ITEMS, MATERIALS OR PRODUCTS TESTED	SPECIFIC TESTS OR PROPERTIES MEASURED	SPECIFICATION, STANDARD METHOD OR TECHNIQUE USED	RANGE (WHERE APPROPRIATE) AND DETECTION LIMIT
Mechanical <sup>F</sup>	Fasteners	Plating thickness, X-ray	QW26	0.000 1 in min
Dimensional Inspection <sup>F</sup>	Threaded Fasteners, Washers, Rivets, and Related Hardware	Diameter, Length, and Other Linear Dimensional Measurements Using Calipers	QW2	0.05 mm to 609.6 mm D.L. = 0.01 mm  0 in to 24 in D.L. = 0.000 5 in
		Diameter, Length, and Other Linear Dimensional Measurements Using Micrometers	QW2	0.2 mm to 50.8 mm D.L. = 0.001 mm  0 in to 2 in D.L. = 0.000 1 in
	Internally Threaded Fasteners	Evaluation Using Threaded Plug (Go and No Go Gages)	QW7	M2 mm to M52 mm  0.86 in to 2 in
	Externally Threaded Fasteners	Evaluation Using Threaded Ring (Go and No Go Gages)	QW7	M2 mm to M36 mm  0.86 in to 1.625 in
	Pitch Diameter	Using Micrometer	QW2	0 in to 2 in (0.2 mm to 50.8 mm)
	Mechanical <sup>F</sup>	Thread Forming Screws	Torsional Breaking Strength	QW18
Externally Threaded Fasteners		Ultimate Tensile Load	QW10, QW11	1 260 N to 300 000 N D.L. = 10 N
Internally Threaded Fasteners		Nut Proof Load	QW12	1 260 N to 300 000 N D.L. = 10 N
Threaded Fasteners, Washers, Rivets, and Related Hardware		Rockwell Hardness	QW9	HRC 20 to HRC 68 HRB 30 to HRB 100 HR15N 69 to HR15N 93 HR30N 42 to HR30N 84 D.L. = 0.1 Respective Hardness Unit
		Micro Indentation Hardness	QW22, QW24	120 HK to 920 HK 105 HK to 940 HV D.L. = 1 Respective Hardness Unit

- The presence of a superscript F means that the laboratory performs testing of the indicated parameter at its fixed location. Example: Outside Micrometer<sup>F</sup> would mean that the laboratory performs this testing at its fixed location.