



## Minimum ultimate tensile loads

according to ISO 898, part 1


### Minimum ultimate tensile loads – ISO metric coarse pitch thread

Thread <sup>1)</sup> d	Nominal stress area $A_{s, nom}$ [mm <sup>2</sup> ]	Minimum ultimate tensile load $F_{m, min}$ ( $A_{s, nom} \times R_{m, min}$ ) [N]								
		Property class								
		4.6	4.8	5.6	5.8	6.8	8.8	9.8	10.9	12.9/12.9
M3	5,03	2010	2 110	2 510	2 620	3 020	4 020	4 530	5 230	6 140
M3,5	6,78	2 710	2 850	3 390	3 530	4 070	5 420	6 100	7 050	8 270
M4	8,78	3 510	3 690	4 390	4 570	5 270	7 020	7 900	9 130	10 700
M5	14,2	5 680	5 960	7 100	7 380	8 520	11 350	12 800	14 800	17 300
M6	20,1	8 040	8 440	10 000	10 400	12 100	16 100	18 100	20 900	24 500
M7	28,9	11 600	12 100	14 400	15 000	17 300	23 100	26 000	30 100	35 300
M8	36,6	14 600 <sup>2)</sup>	15 400	18 300 <sup>2)</sup>	19 000	22 000	29 200 <sup>2)</sup>	32 900	38 100 <sup>2)</sup>	44 600
M10	58,0	23 200 <sup>2)</sup>	24 400	29 000 <sup>2)</sup>	30 200	34 800	46 400 <sup>2)</sup>	52 200	60 300 <sup>2)</sup>	70 800
M12	84,3	33 700	35 400	42 200	43 800	50 600	67 400 <sup>3)</sup>	75 900	87 700	103 000
M14	115	46 000	48 300	57 500	59 800	69 000	92 000 <sup>3)</sup>	104 000	120 000	140 000
M16	157	62 800	65 900	78 500	81 600	94 000	125 000 <sup>3)</sup>	141 000	163 000	192 000
M18	192	76 800	80 600	96 000	99 800	115 000	159 000	–	200 000	234 000
M20	245	98 000	103 000	122 000	127 000	147 000	203 000	–	255 000	299 000
M22	303	121 000	127 000	152 000	158 000	182 000	252 000	–	315 000	370 000
M24	353	141 000	148 000	176 000	184 000	212 000	293 000	–	367 000	431 000
M27	459	184 000	193 000	230 000	239 000	275 000	381 000	–	477 000	560 000
M30	561	224 000	236 000	280 000	292 000	337 000	466 000	–	583 000	684 000
M33	694	278 000	292 000	347 000	361 000	416 000	576 000	–	722 000	847 000
M36	817	327 000	343 000	408 000	425 000	490 000	678 000	–	850 000	997 000
M39	976	390 000	410 000	488 000	508 000	586 000	810 000	–	1 020 000	1 200 000

<sup>1)</sup> Where no thread pitch is indicated in a thread designation, coarse pitch is specified.

<sup>2)</sup> For fasteners with thread tolerance 6az according to ISO 965-4 subject to hot dip galvanizing, reduced values in accordance with ISO 10684.

<sup>3)</sup> For structural bolting 70 000 N (for M12), 95 500 N (for M14) and 130 000 N (for M16).

 To calculate the nominal stress area  $A_{s, nom}$   
Page F.042

### Minimum ultimate tensile loads – ISO metric fine pitch thread

Thread d x P	Nominal stress area $A_{s, nom}$ [mm <sup>2</sup> ]	Minimum ultimate tensile load $F_{m, min}$ ( $A_{s, nom} \times R_{m, min}$ ) [N]								
		Property class								
		4.6	4.8	5.6	5.8	6.8	8.8	9.8	10.9	12.9/12.9
M8x1	39,2	15 700	16 500	19 600	20 400	23 500	31 360	35 300	40 800	47 800
M10x1	64,5	25 800	27 100	32 300	33 500	38 700	51 600	58 100	67 100	78 700
M10x1,25	61,2	24 500	25 700	30 600	31 800	36 700	49 000	55 100	63 600	74 700
M12x1,25	92,1	36 800	38 700	46 100	47 900	55 300	73 700	82 900	95 800	112 000
M12x1,5	88,1	35 200	37 000	44 100	45 800	52 900	70 500	79 300	91 600	107 000
M14x1,5	125	50 000	52 500	62 500	65 000	75 000	100 000	112 000	130 000	152 000
M16x1,5	167	66 800	70 100	83 500	86 800	100 000	134 000	150 000	174 000	204 000
M18x1,5	216	86 400	90 700	108 000	112 000	130 000	179 000	–	225 000	264 000
M20x1,5	272	109 000	114 000	136 000	141 000	163 000	226 000	–	283 000	332 000
M22x1,5	333	133 000	140 000	166 000	173 000	200 000	276 000	–	346 000	406 000
M24x2	384	154 000	161 000	192 000	200 000	230 000	319 000	–	399 000	469 000
M27x2	496	198 000	208 000	248 000	258 000	298 000	412 000	–	516 000	605 000
M30x2	621	248 000	261 000	310 000	323 000	373 000	515 000	–	646 000	758 000
M33x2	761	304 000	320 000	380 000	396 000	457 000	632 000	–	791 000	928 000
M36x3	865	346 000	363 000	432 000	450 000	519 000	718 000	–	900 000	1 055 000
M39x3	1 030	412 000	433 000	515 000	536 000	618 000	855 000	–	1 070 000	1 260 000

## Proof loads of screws

according to ISO 898, part 1

### Proof loads – ISO metric coarse pitch thread

Thread <sup>1)</sup> d	Nominal stress area $A_{s, \text{nom}}$ [mm <sup>2</sup> ]	Proof load $F_p (A_{s, \text{nom}} \times S_{p, \text{nom}}^{4)})$ [N]									
		Property class									
		4.6	4.8	5.6	5.8	6.8	8.8	9.8	10.9	12.9/12.9	
M3	5,03	1130	1560	1410	1910	2210	2920	3270	4180	4880	
M3,5	6,78	1530	2100	1900	2580	2980	3940	4410	5630	6580	
M4	8,78	1980	2720	2460	3340	3860	5100	5710	7290	8520	
M5	14,2	3200	4400	3980	5400	6250	8230	9230	11800	13800	
M6	20,1	4520	6230	5630	7640	8840	11600	13100	16700	19500	
M7	28,9	6500	8960	8090	11000	12700	16800	18800	24000	28000	
M8	36,6	8240 <sup>2)</sup>	11400	10200 <sup>2)</sup>	13900	16100	21200 <sup>2)</sup>	23800	30400 <sup>2)</sup>	35500	
M10	58,0	13000 <sup>2)</sup>	18000	16200 <sup>2)</sup>	22000	25500	33700 <sup>2)</sup>	37700	48100 <sup>2)</sup>	56300	
M12	84,3	19000	26100	23600	32000	37100	48900 <sup>3)</sup>	54800	70000	81800	
M14	115	25900	35600	32200	43700	50600	66700 <sup>3)</sup>	74800	95500	112000	
M16	157	35300	48700	44000	59700	69100	91000 <sup>3)</sup>	102000	130000	152000	
M18	192	43200	59500	53800	73000	84500	115000	–	159000	186000	
M20	245	55100	76000	68600	93100	108000	147000	–	203000	238000	
M22	303	68200	93900	84800	115000	133000	182000	–	252000	294000	
M24	353	79400	109000	98800	134000	155000	212000	–	293000	342000	
M27	459	103000	142000	128000	174000	202000	275000	–	381000	445000	
M30	561	126000	174000	157000	213000	247000	337000	–	466000	544000	
M33	694	156000	215000	194000	264000	305000	416000	–	576000	673000	
M36	817	184000	253000	229000	310000	359000	490000	–	678000	792000	
M39	976	220000	303000	273000	371000	429000	586000	–	810000	947000	

<sup>1)</sup> Where no thread pitch is indicated in a thread designation, coarse pitch is specified.

<sup>2)</sup> For fasteners with thread tolerance 6az according to ISO 965-4 subject to hot dip galvanizing, reduced values in accordance with ISO 10684.

<sup>3)</sup> For structural bolting 50 700 N (for M12), 68 800 N (for M14) and 94 500 N (for M16).

<sup>4)</sup> Value for stress under proof load  $S_{p, \text{nom}}$  and their relation to stress at non-proportional elongation see page F.004, No. 5 in table.

▶ To calculate the nominal stress area  $A_{s, \text{nom}}$   
Page F.042

### Proof loads – ISO metric fine pitch thread

Thread d x P	Nominal stress area $A_{s, \text{nom}}$ [mm <sup>2</sup> ]	Proof load $F_p (A_{s, \text{nom}} \times S_{p, \text{nom}}^{4)})$ [N]									
		Property class									
		4.6	4.8	5.6	5.8	6.8	8.8	9.8	10.9	12.9/12.9	
M8x1	39,2	8820	12200	11000	14900	17200	22700	25500	32500	38000	
M10x1,25	61,2	13800	19000	17100	23300	26900	35500	39800	50800	59400	
M10x1	64,5	14500	20000	18100	24500	28400	37400	41900	53500	62700	
M12x1,25	92,1	20700	28600	25800	35000	40500	53400	59900	76400	89300	
M12x1,5	88,1	19800	27300	24700	33500	38800	51100	57300	73100	85500	
M14x1,5	125	28100	38800	35000	47500	55000	72500	81200	104000	121000	
M16x1,5	167	37600	51800	46800	63500	73500	96900	109000	139000	162000	
M18x1,5	216	48600	67000	60500	82100	95000	130000	–	179000	210000	
M20x1,5	272	61200	84300	76200	103000	120000	163000	–	226000	264000	
M22x1,5	333	74900	103000	93200	126000	146000	200000	–	276000	323000	
M24x2	384	86400	119000	108000	146000	169000	230000	–	319000	372000	
M27x2	496	112000	154000	139000	188000	218000	298000	–	412000	481000	
M30x2	621	140000	192000	174000	236000	273000	373000	–	515000	602000	
M33x2	761	171000	236000	213000	289000	335000	457000	–	632000	738000	
M36x3	865	195000	268000	242000	329000	381000	519000	–	718000	839000	
M39x3	1030	232000	319000	288000	391000	453000	618000	–	855000	999000	

## Materials, heat treatment, chemical compositions

according to ISO 898, part 1

### Steels

Property class	Material and heat treatment	Chemical composition limits (cast analysis, %) <sup>1)</sup>					Tempering temperature °C
		C		P	S	B <sup>2)</sup>	
		min.	max.	max.	max.	max.	
4.6 <sup>3), 4)</sup> 4.8 <sup>4)</sup> 5.6 <sup>3)</sup> 5.8 <sup>4)</sup> 6.8 <sup>4)</sup>	Carbon steel or carbon steel with additives	–	0,55	0,05	0,06	not specified	–
		0,13	0,55	0,05	0,06		
		–	0,55	0,05	0,06		
		0,15	0,55	0,05	0,06		
8.8 <sup>6)</sup>	Carbon steel with additives (e.g. Boron or Mn or Cr), quenched and tempered	0,15 <sup>5)</sup>	0,40	0,025	0,025	0,003	425
	or Carbon steel, quenched and tempered	0,25	0,55	0,025	0,025		
	or Alloyed steel, quenched and tempered <sup>7)</sup>	0,20	0,55	0,025	0,025		
9.8 <sup>6)</sup>	Carbon steel with additives (e.g. Boron or Mn or Cr), quenched and tempered	0,15 <sup>5)</sup>	0,40	0,025	0,025	0,003	425
	or Carbon steel, quenched and tempered	0,25	0,55	0,025	0,025		
	or Alloyed steel, quenched and tempered <sup>7)</sup>	0,20	0,55	0,025	0,025		
10.9 <sup>6)</sup>	Carbon steel with additives (e.g. Boron, Mn or Cr), quenched and tempered	0,20 <sup>5)</sup>	0,55	0,025	0,025	0,003	425
	or Carbon steel, quenched and tempered	0,25	0,55	0,025	0,025		
	or Alloyed steel, quenched and tempered <sup>7)</sup>	0,20	0,55	0,025	0,025		
12.9 <sup>6), 8), 9)</sup>	Alloyed steel, quenched and tempered <sup>7)</sup>	0,30	0,50	0,025	0,025	0,003	425
12.9 <sup>6), 8), 9)</sup>	Carbon steel with additives (e.g. Boron, Mn or Cr or Molybdenum), quenched and tempered	0,28	0,50	0,025	0,025	0,003	380

<sup>1)</sup> In case of dispute, the product analysis applies.

<sup>2)</sup> Boron content can reach 0,005 %, provided that non-effective boron is controlled by addition of titanium and/or aluminium.

<sup>3)</sup> For cold forged fasteners of property classes 4.6 and 5.6, heat treatment of the wire used for cold forging or of the cold forged fastener itself may be necessary to achieve required ductility.

<sup>4)</sup> Free cutting steel is allowed for these property classes with the following maximum sulphur, phosphorus and lead contents: sulphur 0,34%; phosphorus 0,11 %; lead 0,35 %.

<sup>5)</sup> In case of plain carbon boron steel with a carbon content below 0,25 % (cast analysis), the minimum manganese content shall be 0,6 % for property class 8.8 and 0,7 % for 9.8 and 10.9.

<sup>6)</sup> For the materials of these property classes, there shall be a sufficient hardenability to ensure a structure consisting of approximately 90 % martensite in the core of the threaded sections for the fasteners in the «as-hardened» condition before tempering.

<sup>7)</sup> This alloy steel shall contain at least one of the following elements in the minimum quantity given: chromium 0,3%, nickel 0,3%, molybdenum 0,2%, vanadium 0,1%. Where elements are specified in combinations of two, three or four and have alloy contents less than those given above, the limit value to be applied for class determination is 70% of the sum of the individual limit values shown above for the two, three or four elements concerned.

<sup>8)</sup> A metallographically detectable white phosphorous enriched layer is not permitted for property class 12.9/12.9. It shall be detected by a suitable test method.

<sup>9)</sup> Caution is advised when the use of property class 12.9/12.9 is considered. The capability of the fastener manufacturer, the service conditions and the wrenching methods should be considered. Environments may cause stress corrosion cracking of fasteners as processed as well as those coated.

## Characteristics at elevated temperatures

according to ISO 898, part 1

### Influence of elevated temperatures on mechanical properties of fasteners

Elevated temperatures can cause changes in the mechanical properties and in the functional performance of a fastener.

Up to typical service temperatures of 150 °C, no detrimental effects due to a change of mechanical properties of fasteners are known. At temperatures over 150 °C and up to a maximum temperature of 300 °C, the functional performance of fasteners should be ensured by careful examination.

With increasing temperatures, a progressive

- reduction of lower yield strength or stress at 0,2% non-proportional elongation or stress at 0,0048 d non-proportional elongation for finished fasteners, and
- reduction of tensile strength can be experienced. The continuous operating of fasteners at elevated service temperatures can result in stress relaxation, which increases with higher temperatures. Stress relaxation accompanies a loss of clamp force.

Work-hardened fasteners (property classes 4.8, 5.8, 6.8) are more sensitive with regard to stress relaxation compared with quenched and tempered or stress-relieved fasteners.

Care should be taken when lead-containing steels are used for fasteners at elevated temperatures. For such fasteners, a risk of liquid metal embrittlement (LME) should be taken into consideration when the service temperature is in the range of the melting point of lead.

Information for example, in EN 10269 and in ASTM F2281.

## Characteristics at higher strength (if $\geq 1000 \text{ N/mm}^2$ )

Influence of higher screw property class under comprehension of the mechanical stress and environmental conditions.

▶ Risk of hydrogen embrittlement  
Page F.034

